

Solaris - ExoStrong - Arm (20 - 30mmHg)



- ExoStrong garments are designed to move with you. With a functional design at the elbow, wrist and web spaces, you can enjoy the freedom to move
- ExoStrong provides 20 - 30 mmHg of compression
- Available in beige

- ✓ Contracted DVA product
- ✓ Contract approved

Code	Display Name	Colour	Calf/Arm Circumference	Elbow Circumference	Wrist Circumference
FBS303565	Solaris ExoStrong - (20-30mmHg) Wrist to Axilla - Short, Small, Beige, Silicone Top	Beige	270 - 300 mm	240 - 270 mm	150 - 170 mm
FBS303566	Solaris ExoStrong - (20-30mmHg) Wrist to Axilla - Short, Medium, Beige, Knit Top	Beige	310 - 350 mm	270 - 310 mm	170 - 190 mm
FBS303567	Solaris ExoStrong - (20-30mmHg) Wrist to Axilla - Short, Medium, Beige, Silicone Top	Beige	310 - 350 mm	270 - 310 mm	170 - 190 mm
FBS303568	Solaris ExoStrong - (20-30mmHg) Wrist to Axilla - Short, Large, Beige, Knit Top	Beige	350 - 400 mm	310 - 350 mm	200 - 220 mm