

# **Aidacare Aspire A320 Aluminium Bariatric Lifter**



The Aspire A320 will exceed expectations even in the most demanding clinical environments. Its broad base and ample patient clearance compliments the substantial 320 kg safe working load.

- **Ergonomic Handles:** Provide multiple grip points to suit carers of different heights and strengths
- **Ergonomic Handset:** The latest slimline technology from Linak fits neatly in the hand with an intuitive control panel. Battery and service indicator lights assist with service scheduling
- Powered Leg Function: Opens and closes the legs for lifting stability or accessibility
- Quick Release Yoke Attachment: One touch release and attach mechanism, designed for the busy caregiver. Padded yoke for added patient safety
- Build Quality: Strong powder coated aluminium frame with industry leading Linak electronics and warranty provision
- Safety: Critical features include emergency stop button, emergency lowering and anti-entrapment technology, with both patient and caregiver safety at heart
- Intelligent Diagnostics: State of the art Linak Jumbo Care control system.
  Tracks usage and service requirements for safety and compliance
- **Tente Casters:** 2 x 100 mm front castors for reduced rolling resistance under high load. 2 x 125 mm rear locking castors for safety and manoeuvrability
- Item Weight: 63 kg
- Tested and compliant to AS/NZS ISO 10535:2011 (the Australian standard for hoists)

## **Warranty Information**

• Frame: 5 Years

- Ocontracted DVA product
- Ocontract approved

#### ndis

**Item Code:** 

05\_123603161\_0105\_1\_2

Hoist -

Composite:05\_420\_0105\_1\_2 Click here for more information

### **Compliance**

AS/NZS ISO 10535:2011

#### **Accessories**

Click on the cart icon to display the range of optional accessories



• Electronics: 3 Years

• Battery and Handset: 1 Year

Code	Display Name	Total Length	Total Width	Total Height	Lift Range	Leg Gait Range Electric Leg	Safe Working Load	Material
LSS390630	Aidacare Aspire A320 Bariatric Patient Lifter	1505 mm	765 - 1190 mm	1 2165 mm	575 - 1960 mm	640 - 1065 mm True	320 kg	Aluminium