

Aidacare Aspire A320 Aluminium Bariatric Lifter



The Aspire A320 will exceed expectations even in the most demanding clinical environments. Its broad base and ample patient clearance compliments the substantial 320 kg safe working load.

- **Ergonomic Handles:** Provide multiple grip points to suit carers of different heights and strengths
- **Ergonomic Handset:** The latest slimline technology from Linak fits neatly in the hand with an intuitive control panel. Battery and service indicator lights assist with service scheduling
- **Powered Leg Function:** Opens and closes the legs for lifting stability or accessibility
- **Quick Release Yoke Attachment:** One touch release and attach mechanism, designed for the busy caregiver. Padded yoke for added patient safety
- **Build Quality:** Strong powder coated aluminium frame with industry leading Linak electronics and warranty provision
- **Safety:** Critical features include emergency stop button, emergency lowering and anti-entrapment technology, with both patient and caregiver safety at heart
- **Intelligent Diagnostics:** State of the art Linak Jumbo Care control system. Tracks usage and service requirements for safety and compliance
- **Tente Casters:** 2 x 100 mm front castors for reduced rolling resistance under high load. 2 x 125 mm rear locking castors for safety and manoeuvrability
- Item Weight: 63 kg
- Tested and compliant to AS/NZS ISO 10535:2011 (the Australian standard for hoists)

Warranty Information

- Frame: 5 Years

✓ Contracted DVA product

✓ Contract approved

ndis

Item Code:

05_123603161_0105_1_2

Hoist –

Composite:05_420_0105_1_2

Click [here](#) for more information

Compliance

AS/NZS ISO 10535:2011

Accessories

Click on the cart icon to display the range of optional accessories

- Electronics: 3 Years
- Battery and Handset: 1 Year

Code	Display Name	RRP	Box Quantity	Total Length	Total Width	Total Height	Lift Range	Leg Gait Range	Electric Leg	Safe Working Load	Material
LSS390630	Aidacare Aspire A320 Bariatric Patient Lifter	7229	1	1505 mm	765 - 1190 mm	2165 mm	575 - 1960 mm	640 - 1065 mm	True	320 kg	Aluminium