

Aidacare Medication Sachet Cart



- The Aidacare Medication Sachet Cart offers large capacity and flexible organisation of treatment supplies in 3" and 9" seamless drawers, featuring a unique integrated divider system
- Aidacare carts are designed to offer an attractive, practical and durable cart with multiple configurations to enable the efficient organisation and delivery of medication and equipment
- Robust panels to minimise dents and scratches
- Includes an expansive work area, with a slide out work surface if more space is needed
- Easy roll 125 mm castors
- The durable steel frame and unique spread caster position ensure stability, making the cart easy to move and control
- Choose from an array of accessories to optimise the cart for your facility's treatment needs
- **Standard Inclusions:** Drawer Dividers and Extended Sliding Surface.
- Lock System Options:
 - **Key lock:** The key lock system is a proven method of securing your medical cart and providing the level of security necessary
 - **Digital lock:** A user friendly system where the cart is locked and unlocked using a pre-set code ensuring ease of access and the security required in clinical environments. The digital lock is robust and waterproof
- Standard drawer configuration detailed below
- **Small Medication Sachet Cart:**
 - 5 small 3' drawer (7 cm)
 - 1 large 9' drawer (25 cm)
- **Medium Medication Sachet Cart:**
 - 6 small 3' drawers (7 cm)



Accessories

Click on the cart icon to display the range of optional accessories

- 1 large 9' drawer (25 cm)

Warranty Information

- Structural: 5 Years Warranty
- Digital Lock: 2 Years Warranty
- Accessories: 1 Year Warranty

Code	Display Name	Total Length	Total Width	Total Height
WAT909520	Aidacare Medication Sachet Cart - Small - Digital Lock	790 mm	610 mm	900 mm
WAT909570	Aidacare Medication Sachet Cart - Small - Key Lock	790 mm	610 mm	900 mm
WAT909530	Aidacare Medication Sachet Cart - Medium - Digital Lock	790 mm	610 mm	1000 mm
WAT909580	Aidacare Medication Sachet Cart - Medium - Key Lock	790 mm	610 mm	1000 mm