

Aspire Air Lift Chair



- Powered lift armchair assists the user in sitting and standing transfers
- Quiet and smooth lift system with infinite rise and recline positions for ultimate comfort
- Petite chair - The standard seat depth is 460mm adjustable by increase the seat depth by 50mm
- Large Chair - The standard seat depth is 510mm adjustable by decreasing the seat depth by 50mm
- Medical grade Dartex upholstery - Anti-microbial & 3 way stretch
- Backrest characteristics - Multilayer foam and fibre pillow sections provide a soft, breathable and supportive surface ideal for extended periods of sitting
- Contoured air bladder in the seating surface can be easily inflated and adjusted with integrated hand pump - stowed and concealed within chair when not in use
- Removable backrest and seat cushion for easy cleaning & maintenance
- Leverage grips promote user independence during the sit-to-stand movement
- Comes standard with 100 mm swivel castors for mobility
- Large side pocket for convenient storage

✔ Contracted DVA product

✔ Contract approved

Support @ Home

Function: Sitting furniture

Category: Under advice

Click [here](#) for more information

NDIS

Item Code:

05_180903180_0103_1_2

Click [here](#) for more information

Compliance

ISO13934-1 / ISO13937-1 / BS6807 / BS7175

Warranty Information

- 2 Years

| Code | Display Name | Safe Working Load | Seat Depth | Seat Width | Seat To Floor Height | Seat To Footrest | Backrest Height |
|-----------|---|-------------------|--------------|------------|----------------------|------------------|-----------------|
| CHP198880 | Aspire Air Lift Chair - Large - Dual Action | 140 kg | 460 - 510 mm | 510 mm | 480 mm | 480 mm | 610 mm |

| Code | Display Name | Safe Working Load | Seat Depth | Seat Width | Seat To Floor Height | Seat To Footrest | Backrest Height |
|-----------|--|-------------------|--------------|------------|----------------------|------------------|-----------------|
| CHP198865 | Aspire Air Lift Chair - Petite - Space Saver | 140 kg | 460 - 510 mm | 450 mm | 480 mm | 480 mm | 610 mm |