

Solaris - ExoStrong - Below Knee



- From the MTP to just below the knee bend, these ready-to-wear flat-knit garments offer maximum containment
- Heel seam provides an anatomical fit and helps ensure the garment is donned properly
- Flat, reinforced edges help reduce irritation and rolling
- Provides a comfortable fit while standing and prevents bulking at the ankle
- Made with fibres that combine a soft, tactile feel with moisture wicking and temperature control

- ✓ Contracted DVA product
- ✓ Contract approved

Code	Display Name	Colour
FBS309030	ExoStrong - Below Knee - Short - Small - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309040	ExoStrong - Below Knee - Short - Small - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309050	ExoStrong - Below Knee - Short - Small - Black - 20-30 mmHg - Open - Knit	Black
FBS309060	ExoStrong - Below Knee - Short - Small - Black - 20-30 mmHg - Open - Silicone	Black
FBS309070	ExoStrong - Below Knee - Short - Medium - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309080	ExoStrong - Below Knee - Short - Medium - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309090	ExoStrong - Below Knee - Short - Medium - Black - 20-30 mmHg - Open - Knit	Black

Code	Display Name	Colour
FBS309100	ExoStrong - Below Knee - Short - Medium - Black - 20-30 mmHg - Open - Silicone	Black
FBS309110	ExoStrong - Below Knee - Short - Large - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309120	ExoStrong - Below Knee - Short - Large - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309130	ExoStrong - Below Knee - Short - Large - Black - 20-30 mmHg - Open - Knit	Black
FBS309140	ExoStrong - Below Knee - Short - Large - Black - 20-30 mmHg - Open - Silicone	Black
FBS309150	ExoStrong - Below Knee - Short - X-Large - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309160	ExoStrong - Below Knee - Short - X-Large - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309170	ExoStrong - Below Knee - Short - X-Large - Black - 20-30 mmHg - Open - Knit	Black
FBS309180	ExoStrong - Below Knee - Short - X-Large - Black - 20-30 mmHg - Open - Silicone	Black
FBS309190	ExoStrong - Below Knee - Short - XX-Large - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309200	ExoStrong - Below Knee - Short - XX-Large - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309210	ExoStrong - Below Knee - Short - XX-Large - Black - 20-30 mmHg - Open - Knit	Black
FBS309220	ExoStrong - Below Knee - Short - XX-Large - Black - 20-30 mmHg - Open - Silicone	Black
FBS309230	ExoStrong - Below Knee - Average - Small - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309240	ExoStrong - Below Knee - Average - Small - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309250	ExoStrong - Below Knee - Average - Small - Black - 20-30 mmHg - Open - Knit	Black
FBS309260	ExoStrong - Below Knee - Average - Small - Black - 20-30 mmHg - Open - Silicone	Black

Code	Display Name	Colour
FBS309270	ExoStrong - Below Knee - Average - Medium - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309280	ExoStrong - Below Knee - Average - Medium - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309290	ExoStrong - Below Knee - Average - Medium - Black - 20-30 mmHg - Open - Knit	Black
FBS309300	ExoStrong - Below Knee - Average - Medium - Black - 20-30 mmHg - Open - Silicone	Black
FBS309310	ExoStrong - Below Knee - Average - Large - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309320	ExoStrong - Below Knee - Average - Large - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309330	ExoStrong - Below Knee - Average - Large - Black - 20-30 mmHg - Open - Knit	Black
FBS309340	ExoStrong - Below Knee - Average - Large - Black - 20-30 mmHg - Open - Silicone	Black
FBS309350	ExoStrong - Below Knee - Average - X-Large - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309360	ExoStrong - Below Knee - Average - X-Large - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309370	ExoStrong - Below Knee - Average - X-Large - Black - 20-30 mmHg - Open - Knit	Black
FBS309380	ExoStrong - Below Knee - Average - X-Large - Black - 20-30 mmHg - Open - Silicone	Black
FBS309390	ExoStrong - Below Knee - Average - XX-Large - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309400	ExoStrong - Below Knee - Average - XX-Large - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309410	ExoStrong - Below Knee - Average - XX-Large - Black - 20-30 mmHg - Open - Knit	Black
FBS309420	ExoStrong - Below Knee - Average - XX-Large - Black - 20-30 mmHg - Open - Silicone	Black
FBS309430	ExoStrong - Below Knee - Tall - Small - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309440	ExoStrong - Below Knee - Tall - Small - Beige - 20-30 mmHg - Open - Silicone	Beige

Code	Display Name	Colour
FBS309450	ExoStrong - Below Knee - Tall - Small - Black - 20-30 mmHg - Open - Knit	Black
FBS309460	ExoStrong - Below Knee - Tall - Small - Black - 20-30 mmHg - Open - Silicone	Black
FBS309470	ExoStrong - Below Knee - Tall - Medium - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309480	ExoStrong - Below Knee - Tall - Medium - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309490	ExoStrong - Below Knee - Tall - Medium - Black - 20-30 mmHg - Open - Knit	Black
FBS309500	ExoStrong - Below Knee - Tall - Medium - Black - 20-30 mmHg - Open - Silicone	Black
FBS309510	ExoStrong - Below Knee - Tall - Large - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309520	ExoStrong - Below Knee - Tall - Large - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309530	ExoStrong - Below Knee - Tall - Large - Black - 20-30 mmHg - Open - Knit	Black
FBS309540	ExoStrong - Below Knee - Tall - Large - Black - 20-30 mmHg - Open - Silicone	Black
FBS309550	ExoStrong - Below Knee - Tall - X-Large - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309560	ExoStrong - Below Knee - Tall - X-Large - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309570	ExoStrong - Below Knee - Tall - X-Large - Black - 20-30 mmHg - Open - Knit	Black
FBS309580	ExoStrong - Below Knee - Tall - X-Large - Black - 20-30 mmHg - Open - Silicone	Black
FBS309590	ExoStrong - Below Knee - Tall - XX-Large - Beige - 20-30 mmHg - Open - Knit	Beige
FBS309600	ExoStrong - Below Knee - Tall - XX-Large - Beige - 20-30 mmHg - Open - Silicone	Beige
FBS309610	ExoStrong - Below Knee - Tall - XX-Large - Black - 20-30 mmHg - Open - Knit	Black
FBS309620	ExoStrong - Below Knee - Tall - XX-Large - Black - 20-30 mmHg - Open - Silicone	Black

