

Solaris ReadyWrap - Foot



- The Solaris Lymphoedema ReadyWrap Foot Wrap has a simple two-strap design to fit into most shoes and allow for easier donning
- Its left and right specific design and medial dart enhance contouring
- The breathable material feels soft against the skin
- Provides mild to moderate levels of compression
- Intended Uses:
 - Maintain reduced fluid volume and shape of upper and lower extremity limbs
 - Management of lymphedema
 - Relief of leg fatigue and heaviness
 - Assists in the management of some symptoms of venous ulcers
 - Assists in helping limit venous ulcer recurrence

✔ Contracted DVA product

✔ Contract approved

Support @ Home

Function: Supporting and stimulating blood circulation

Category: Low risk

Click [here](#) for more information

Code	Display Name	Total Length	Colour	Ankle Circumference
FBS303593	Solaris ReadyWrap - Large - Left - Beige	260 mm	Beige	250 - 330 mm
FBS303594	Solaris ReadyWrap - Large - Left - Black	260 mm	Black	250 - 330 mm
FBS303595	Solaris ReadyWrap - Medium - Left - Beige	230 mm	Beige	200 - 280 mm
FBS303597	Solaris ReadyWrap - Small - Left - Beige	210 mm	Beige	180 - 230 mm
FBS303598	Solaris ReadyWrap - Small - Left - Black	210 mm	Black	180 - 230 mm
FBS303599	Solaris ReadyWrap - Xlarge - Left - Beige	290 mm	Beige	300 - 380 mm
FBS303600	Solaris ReadyWrap - Xlarge - Left - Black	290 mm	Black	300 - 380 mm

Code	Display Name	Total Length	Colour	Ankle Circumference
FBS303601	Solaris ReadyWrap - Large - Right - Beige	260 mm	Beige	250 - 330 mm
FBS303602	Solaris ReadyWrap - Large - Right - Black	260 mm	Black	250 - 330 mm
FBS303603	Solaris ReadyWrap - Medium - Right - Beige	230 mm	Beige	200 - 280 mm
FBS303604	Solaris ReadyWrap - Medium - Right - Black	230 mm	Black	200 - 280 mm
FBS303605	Solaris ReadyWrap - Small - Right - Beige	210 mm	Beige	180 - 230 mm
FBS303606	Solaris ReadyWrap - Small - Right - Black	210 mm	Black	180 - 230 mm
FBS303607	Solaris ReadyWrap - Xlarge - Right - Beige	290 mm	Beige	300 - 380 mm
FBS303608	Solaris ReadyWrap - Xlarge - Right - Black	290 mm	Black	300 - 380 mm