

## Meiko TopLine 20XL Sanitiser



- Packed with powerful technology, the TopLine bedpan washer-disinfectors aim to eliminate the risk of infections stemming from hospital dirty utility rooms
- Floor Mounted
- Side-by-side for Increased Capacity & System-redundancy if failure event
- Patented complete steam impermeability system – No risk of germ discharge, highest level of work and hygiene safety
- Controllable main telescopic rotary nozzle – Optimised internal cleaning of the care utensils
- Thorough cleaning with power nozzle system
- Air drying and cooling with filtered air (HEPA filter) produces hygienically clean results
- Replaceable and simple to change HEPA filter
- System disinfection of all water-carrying lines and protects from recontamination
- Patented control of the freely selectable A0 value (60 to 3000) and monitored by temperature sensors which crosscheck each other's readings guarantees disinfection safety
- Hygienic safety due to A0-value control system to DIN EN ISO 15883
- A0 value in the display (actual and target value)
- Supply disconnection to EN 1717 type AA
- Integrated steam generator/water tank, which means shortest possible programme cycles
- Disinfection process control with temperature sensors. The control software monitors and assesses the control process
- Maximum flexibility due to multifunctional utensils holder concept



Code	Display Name	Total Length	Total Width	Total Height
UPM200140	Meiko Sanitiser - TopLine 20 XL	450 mm or 588 mm	1000 mm	1730 mm
UPM200150	Meiko Sanitiser - TopLine 20 XL AT - with Auto Door & Foot	450 mm or 588 mm	1000 mm	1730 mm