

## Panamatic Optima 3



- In busy sluiceroom situations, the Panamatic Optima 3 excels. The Optima 3 is the hot and cold water cousin of the maxi. The large wash chamber accommodates a range of utensils and urine bottles per cycle
- Wash Performance - Efficient cleaning nozzles and water jet pressure maximise results in the flush wash cycle. Hot & cold water connection
- Cycle time - Wash and temperature control efficiency provides for quicker turnaround
- Hands free opening - Means easier loading when hands are busy carrying dirty utensils and urine bottles
- Large Chamber - The wash chamber and large opening allow a greater combination of larger utensils and urine bottles in one wash cycle. This includes larger items like ward cleaner's buckets, commode bowls and toilet seat raisers for sanitising
- Panamatic cycle - Flush, wash and thermal sanitisation. High pressure rotating wash nozzles and strategically sited spray jets ensure superior wash performance. Automatic dosing at 40 ml of EcoWash per cycle. Cold water flush / wash - steam cycle - cool-down rinse
- Steam disinfection cycle - the Maxi thermal sanitiser delivers sanitisation at the steam disinfection level of > Ao 700 being 85° at 75 seconds for utensils in its chamber
- Electrical supply: Single Phase 230 V, 13 AMP
- Electrical output/input: Motor - 0.75 KW, Heater - 2.5 KW
- Water supply: 15 mm Hot & Cold water 1 - 6 bar
- Soil connection: 110 mm connections supplied
- Operation cycle time: Approx 5 mins - 30 ml Ecowash
- Steam disinfection: Exceeds Ao 700, 85° x 75 secs



### Compliance

ISO 15883/AS 4187:2019

## Warranty Information

- 1 Year

Code	Display Name
UPM100260	DDC Bedpan Washer Sanitiser - Optima 3