

## Ceiling Hoist - Liko - Likorall 243 ES



- The Likorall™ 243 overhead lift system provides strong and secure lifting for those who need enhanced lifting power
- The lift motor is installed in our standard rail system and has a lifting capacity of 230 kg (507 lb)
- Like the other ES-class motors, the Likorall 243 ES system allows for movement of the lift motor along the rail electronically with a transfer motor, or to control the rail's electrical switches via a wireless hand control option
- Its safety features include a patented safety drum with speed limiter and electrical emergency lowering
- The motor's 200 cm (80") lifting interval handles lifts from the floor in most environments, and the motor can be equipped with a special carriage for easy room-to-room transfers. A quick-release changing sling bar adds to its appeal

### Warranty Information

- 2 years Motor, 1 year Battery and Handset



Contract approved

### Support @ Home

**Function:** Lifting persons

**Category:** Prescribed

Click [here](#) for more information

### Compliance

AS/NZS ISO 10535:2011

Code	Display Name
LIC359537	Likorall 243 ES -230Kg