

## Avantgarde A4



**ottobock.**

- Handy Back bag: The back bag integrated into the back upholstery is easy for the user to reach and is equipped with a magnetic closure
- New Push Handles : The new short push handles are optimised for low weight. Folding push handles are available as well
- Desk side panel with armrest: The desk side panel offers numerous functions to position the forearms and for transfers. The armrest features multiple adjustment possibilities, while the side panel can swing away to the rear, behind the back, and is removable
- Elevating leg support: The height-adjustable leg support effectively supports leg positioning up to the horizontal
- Integrated Pockets: Two pockets below the seat upholstery provide space for the storage of personal items, protecting them against third-party access
- Small Folding Size: The Avantgarde stands out for its extremely small folding size. Straight leg supports further reduce the folding size by a significant amount
- Anti-tipper: The anti-tipper is spring-loaded, with multiple adjustment possibilities. This ensures straightforward operation and the tip-resistance of the wheelchair is assured even with extreme settings
- Telescoping push handles: Telescoping push handles ensure that the attendant can bring the handles to an ergonomic height for pushing in a few simple steps.
- High number of rear wheel positions
- Removable footrest holders can be swung in and out
- Variability thanks to numerous options
- Minimised torsional forces in the frame
- Swivel segment easy to activate with a lever

✔ Contract approved

### Support @ Home

**Function:** Manual wheelchairs

**Category:** Prescribed

Click [here](#) for more information

### NDIS

**Item Code:**

05\_122203111\_0105\_1\_2

**Wheelchair Manual –**

**Composite:**05\_417\_0105\_1\_2

Click [here](#) for more information

## Warranty Information

- 2 Years

Code	Display Name	Total Width	Total Height	Safe Working Load	Seat Depth	Seat Width
MWC427103	Avantgarde A4	490 - 725 mm	580 - 1100 mm	100 / 140 kg	360 - 520 mm	320 - 500 mm