

Outdoor Sensor Light



- Sensing angle up to 120 degrees
- Sensing range up to 12 m
- Sensor can be pointed in the direction required
- Manual override light can be switched to stay on
- Selectable Motion Timer: 1, 5, or 10 minutes
- Selectable timer choose how long you wish the light to remain on after detecting movement
- Dual pulse technology minimise false triggering
- Dusk to dawn operation will not come on during the day
- Bulbs 2 x PAR38 150 W bulbs
- Bulbs Screw-type bulbs

Warranty Information

• 1 Year

Code Display Name

DLG272215 Outdoor Sensor Light - Twin 150watt Sensor Light - 12metres



ndis

Item Code:

05_098800044_0103_1_2 Click <u>here</u> for more information

Compliance

No applicable compliance standard