


## Aspire MAXI Lifestyle Mattress



The LIFECOMFORT® MAXI Lifestyle is a robust support surface designed for larger users up to 350kg. Three foam tiers provide immersion for pressure reduction and comfort as well as support. Side wall foam density is strengthened to assist heavier users for bed entry and exit. Fitted with superior, hospital-grade polyurethane coated covers designed to withstand the rigors of usage and cleaning requirements in Home Care, Aged Care and up to Acute Care environments.



Contract approved

- **Durable Hospital Grade Foam** that is treated for antimicrobial and antibacterial properties
- **Breathable, 4-Way Stretch Waterproof Cover** to reduce shear, friction and maintain skin microclimate
- **Medical Grade Waterfall Cover** is fully-welded over the zipper to maximise infection control
- **Asset Management Ready** with unique batch and serial numbers printed on all covers
- **Carry Handle** - Integrated handles for safe manual handling
- **Hospital Grade** - Suitable for bleach concentrations up to 10,000 ppm
- **4-sided Zipper** - Easily removed for effective cleaning
- **4-way Stretch** - For shear mitigation and friction reduction
- Immersive surface contours and cradles around the user for personalised pressure relief and comfort
- Machine Washable Covers: Up to 95°
- **Foam Layers:**
  - COMFORT LAYER - Transition layer that boosts visco layer efficiency under higher weight loads
  - SUPPORT LAYER - High resilience foam for diverse user weight and distribution
  - SAFETY & SUPPORT BASE - Strong base support for maximum

- durability
- INTEGRATED SIDE WALLS - Strong rigid side layers for transfer efficiency and safety
- **Applications** - Pressure Care: Medium - High
  - Hospital
  - Aged Care
  - Home Care
  - Palliative Care
  - Bariatric Care

## Warranty Information

- 5 years foam
- 4 years cover

Code	Display Name	RRP	Box Quantity	Total Length	Total Width	Total Height	Safe Working Load
BEM046710	Aspire MAXI Lifestyle Mattress - Super King	1639	1	2060 mm	1150 mm	200 mm	150 - 350 kg